


Beam Clamp with Swivel, Electrogalvanized, 24 mm Max Flange



KATALOGNUMMER

HB2

FUNKTIONER

Swivel beam clamp

Suitable for mounting onto sloped steel structures

Includes M10 nut and washer



PRODUKTEGENSKABER

Artikelnummer: 336030

Materiale: Stål

Finish: Electrogalvanized

Flange Thickness (FT): 24 mm Max


Torque (TQ): 6 N·m

Angle 1 (a1): 45 ° Min

Angle 2 (a2): 30 ° Max

YDERLIGERE PRODUKTOPLYSNINGER

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

