

Internal Strut Beam Clamp

KATALOGNUMMER

INC8

FUNKTIONER

Mounts strut within beams



PRODUKTEGENSKABER

Artikelnummer: 336290

Materiale: Spring Steel

Finish: nVent CADDY Armour

Strut Type: A (41 x 41 mm);C (21 x 41 mm)

A: 13 mm

Screw Diameter (Sc): 8



Screw Length (L): 25mm

Torque (TQ): 6 N·m

Static Load: 450N

YDERLIGERE PRODUKTOPLYSNINGER

Strut channel must be cut 3/4" (20mm) shorter than the inner distance between the two beam flanges in order to accommodate the clamps.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

