

Strut Cantilever Arm Type AA, Slotted, HD, 750 mm x 41 mm x 82 mm x 2.5 mm



KATALOGNUMMER

KAA25H0750HD

FUNKTIONER

Channel welded back to back

Welded on flat mounting plate



PRODUKTEGENSKABER

Artikelnummer: 311431

Strut Type: AA (83 x 41 mm)

Materiale: Stål

Finish: Hot-Dip Galvanized

Length (L): 750mm

Height (H): 165 mm

Width (W): 50 mm

A: 22 mm

B: 41 mm

C: 82 mm




D: 50 mm

E: 8 mm

Y: 14 x 27 mm

Thickness (T): 2.5 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

