

Gravity Toggle with Rubber Washer, M10 Rod, 100 mm

KATALOGNUMMER


MTVB10100

FUNKTIONER

Complete with rod, nut, washer and load distribution block

Threaded rod is secured against unintentional removal

Approved for use in stationary fire protection systems (for pipes up to 2")



PRODUKTEGENSKABER

Artikelnummer: 584465

Materiale: Stål

Finish: Electro galvanized

Rod Size (RS): 10

Length (L): 100mm

Drill Bit Diameter: 25mm


Static Load: 800N

Ultimate Static Load (F): 20kN

YDERLIGERE PRODUKTOPLYSNINGER

Static Load represents the maximum recommended load when fixed to a trapezoidal sheet.

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

