

# Strut Nut without Spring, Steel, Hot-dip galvanized, M6 Rod, 6 mm

## KATALOGNUMMER

**NUTM6HD**

## FUNKTIONER

Used to create metal frames with nVent CADDY Eristrut channels



## PRODUKTEGENSKABER

Artikelnummer: 315000

Materiale: Stål

Finish: Hot-Dip Galvanized

Static Load Safety Factor: 3:1



Rod Size (RS): 6

Thickness (T): 6 mm

Torque (TQ): 12 N·m

| Pull-Out Strength |              |                   |        |        |
|-------------------|--------------|-------------------|--------|--------|
| Part Number       | Channel Type | Channel Thickness |        |        |
|                   |              | 2,5 mm            | 2 mm   | 1,5 mm |
| NUTM6xx           | A, C         | 2000 N            | 2000 N | 2000 N |
|                   | D, E         | 2000 N            | -      | -      |
| NUTM8xx           | A, C         | 3330 N            | 3330 N | 3330 N |
|                   | D, E         | 3330 N            | -      | -      |
| NUTM10xx          | A, C         | 4890 N            | 4440 N | 4440 N |
|                   | D, E         | 4890 N            | -      | -      |
| NUTM12xx          | A, C         | 4890 N            | 4660 N | 4440 N |
|                   | D, E         | 3670 N            | -      | -      |
| NUTM12Txx         | A            | 5670 N            | 5050 N | 4440 N |
|                   | D, E         | 4250 N            | -      | -      |
| NUTM16xx          | A            | 5670 N            | 4660 N | 4440 N |
|                   | D, E         | 4250 N            | -      | -      |

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

