

OCDC Deck Hanger, 1–2.5 mm Flange



KATALOGNUMMER

OCDC68MM

FUNKTIONER

Provide a mobile mounting hole

Attaches to decking without having to drill or punch holes

Secured between the overlap of two steel sheets

PRODUKTEGENSKABER

Artikelnummer: 160700

Materiale: Stål

Finish: nVent CADDY Armour

Hole Size (HS): 6.8 mm


Flange Thickness (FT): 1.0 - 2.5 mm

B: 54 mm

C: 46 mm

X: 13 x 8.5 mm

Static Load: 400N



nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Germany:
800 1890272
Other Countries:
+31 13 5835404

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

