

PBF Two Hole Base Plate for Threaded Rod, Steel, EG, M10 Rod, 80 mm

KATALOGNUMMER

PBRM10L80

FUNKTIONER

Light duty with two holes and one nut/adaptor



PRODUKTEGENSKABER

Artikelnummer: 587135

Materiale: Stål

Finish: Electrogalvanized

Rod Size (RS): 10

Length (L): 80mm

Width (W): 30 mm



Thickness (T): 3 mm

A: 50 mm

B: 18 mm

C: 9 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

