

Threaded Bridle Ring, 12 mm dia, M6 Screw, Metal



KATALOGNUMMER

PTB6

FUNKTIONER

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

PRODUKTEGENSKABER

Artikelnummer: 172921

Materiale: Stål

Finish: Electrogalvanized

Diameter: 12 mm

Screw Diameter: 6

Screw Type: Metal

Screw Length: 32mm

Ultimate Static Load: 220N

YDERLIGERE PRODUKTOPLYSNINGER

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDDT](https://www.nvent.com/ENDDT)

