

nVent CADDY Pyramid Tool-Free Pipe Clamp, 21.3–60.3 mm OD



KATALOGNUMMER

PTF2C

FUNKTIONER

Push-in clamps install without the need for additional tools or strut clamps

Clamps come in two different sizes to fit project needs

Plastic clamps and base will not corrode pipe

PRODUKTEGENSKABER

Artikelnummer: 360485

Materiale: Nylon

Temperature: -45 to 65 °C



Outer Diameter (OD): 21.3 - 60.3 mm

Length (L): 81.3mm

Width (W): 19.1 mm

A: 9.5 mm

Unit Weight: 0.02 kg



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

