

Quick Strut Nut, M10 Rod



KATALOGNUMMER

QSNM10EG

FUNKTIONER

Provides fast universal attachment of threaded rod and hardware to standard strut profiles

Pre-assembled slide nut ready to use out of the box

Spring retains assembly in place until hardware is tightened

PRODUKTEGENSKABER

Artikelnummer: 592920

Materiale: Stål

Finish: Electrogalvanized

Rod Size (RS): 10

A: 8 mm

B: 4 mm

C: 41 mm

Torque (TQ): 55 N·m




Static Load 1 (F1): 4400N

Static Load 2 (F2): 4400N

Static Load 3 (F3): 4900N

YDERLIGERE PRODUKTOPLYSNINGER

Static Load 1 represents 1.5 mm strut channel thickness. Static Load 2 represents 2.0 mm strut channel thickness. Static Load 3 represents 2.5 mm strut channel thickness.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

