


# Bolt Expansion Anchor, Steel, EG, M12 Rod, 110 mm

## KATALOGNUMMER

**SABM12015**

## FUNKTIONER



Heavy duty wedge anchor

For cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

Approved for use in seismic design category C1 & C2 (for Drill Bit Diameters 8 mm and greater)



## PRODUKTEGENSKABER

Artikelnummer: 402170

Materiale: Stål

Finish: Electrogalvanized

Thread Size (TS): M12

Length (L): 110mm


Embedment Depth: 80 mm

A: 14 mm

Drill Bit Diameter: 12mm

| Characteristic Axial Loads from ETA-12/0397 |                         |                             |
|---------------------------------------------|-------------------------|-----------------------------|
| Part Number                                 | Cracked Concrete C20/25 | Non-Cracked Concrete C20/25 |
| SABM8010                                    | 2.4 kN                  | 3.6 kN                      |
| SABM8050                                    | 2.4 kN                  | 3.6 kN                      |
| SABM10010                                   | 4.3 kN                  | 7.6 kN                      |
| SABM10050                                   | 4.3 kN                  | 7.6 kN                      |
| SABM12015                                   | 7.6 kN                  | 11.9 kN                     |
| SABM12050                                   | 7.6 kN                  | 11.9 kN                     |
| SABM16025                                   | 11.9 kN                 | 16.7 kN                     |
| SABM20030                                   | 14.3 kN                 | 23.8 kN                     |
| SABM8010S6                                  | 2.4 kN                  | 4.3 kN                      |
| SABM8050S6                                  | 2.4 kN                  | 4.3 kN                      |
| SABM10010S6                                 | 4.3 kN                  | 7.6 kN                      |
| SABM10050S6                                 | 4.3 kN                  | 7.6 kN                      |

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

