

SIT CLIM Insulated Pipe Clamp with Rubber Ends, 13 mm Insulation, 10 mm OD



KATALOGNUMMER

SCLI13I0010

FUNKTIONER

Pre-mounted with steel two screw pipe clamp

Fire rating B2 acc. to DIN 4102-1

Fire rating M1 acc. to NFP 92-501

PRODUKTEGENSKABER

Artikelnummer: 580091

Insulation Thickness: 13 mm

Materiale: Stål;Polyisocyanurate

Finish: Electrogalvanized

Density: 80 kg/m³

Compressive Strength: 520 kPa @ 23 °C


Thermal Conductivity: 0.03 W/m-K @ 10 °C

Temperature: -40 to 90 °C

Outer Diameter (OD): 10 mm

Rod Size (RS): M8;M10

B: 50 mm



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

