

# SIT CLIM Insulated Pipe Clamp with Rubber Ends, 13 mm Insulation, 12 mm OD



## KATALOGNUMMER

**SCLI13I0012**

## FUNKTIONER

Pre-mounted with steel two screw pipe clamp

Fire rating B2 acc. to DIN 4102-1

Fire rating M1 acc. to NFP 92-501

## PRODUKTEGENSKABER

Artikelnummer: 580092

Insulation Thickness: 13 mm

Materiale: Stål;Polyisocyanurate

Finish: Electrogalvanized

Density: 80 kg/m<sup>3</sup>

Compressive Strength: 520 kPa @ 23 °C


Thermal Conductivity: 0.03 W/m-K @ 10 °C

Temperature: -40 to 90 °C

Outer Diameter (OD): 12 mm

Rod Size (RS): M8;M10

B: 50 mm



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

