

Tool-free 1.5mm Wire Rope Hanger Kit M6 with Hook End-Fitting - 1m Long - 19.5kg

KATALOGNUMMER

SLDM615L1

FUNKTIONER

Complete system includes wire, locking device and pre-assembled hook end fitting

Ideal for supporting lighting, ductwork and other installation projects

Sleek, low-profile locking device reduces visual impact

Keyless locking device is adjustable even after installation



PRODUKTEGENSKABER

Artikelnummer: 196028

Materiale: Stål

Finish: Electro galvanized

Static Load Safety Factor: 5:1

Wire Rope Diameter: 1.5 mm

Wire Rope Length: 1m

A: 58.4 mm

B: 22.9 mm

C: 6.4 mm



Static Load: 195N

Rod Size (RS): 6

Length (L): 7mm

Height (H): 24.5 mm

Width (W): 9.2 mm



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

