

nVent CADDY Speed Link SLK with Wedge Anchor, 1.5 mm Wire, 2 m Length

KATALOGNUMMER

SLK15L2WA6

FUNKTIONER

Complete system includes wire, locking device and wedge anchor from fischerwerke GmbH & Co. KG

Quickly and easily attaches into cracked and non-cracked concrete

No special tools required

ETA 06/0175 approval available from fischerwerke GmbH & Co. KG



PRODUKTEGENSKABER

Artikelnummer: 196671

Materiale: Stål;Polypropylene;Zinc Alloy

Finish: Electrogalvanized

Static Load Safety Factor: 5:1

Wire Rope Diameter: 1.5 mm

Wire Rope Length: 2m

Length (L): 54mm

Height (H): 55 mm

Width (W): 19 mm

Thickness (T): 12.5 mm




Angle (a): 90 ° Max

Static Load: 195N

Drill Bit Diameter: 6mm

Drill Hole Depth: 31mm

Embedment Depth: 25 mm Min



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

