

# nVent CADDY Speed Link SLK with Drop Wire Clip, 3 mm Wire, 3 m Length



## KATALOGNUMMER

**SLK3L3DW6**

## FUNKTIONER

Complete system includes wire, locking device and pre-assembled drop wire clip end fitting for catenary cable

Can be used to hang services from catenary cable or act as an intermediate support to reduce sag and tension

Easily snaps onto catenary cable and locks in place when closed

Tool-free clip can be hand-closed on the catenary wire

## PRODUKTEGENSKABER

Artikelnummer: 196844

Materiale: Stål;Spring Stål;Polypropylene;Zinc Alloy

Finish: Electroalvanized;nVent CADDY Armour

Static Load Safety Factor: 5:1

Wire Rope Diameter: 3 mm

Wire Rope Length: 3m

A: 70 mm

B: 20 mm

C: 25 mm

Diameter (Ø): 6 mm

Height (H): 62 mm

Width (W): 24 mm

Thickness (T): 16 mm

Angle (a): 90 ° Max

Static Load: 700N

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDDT](http://nVent.com/ENDDT)

