

SNSW Flanged Nut, M10 Rod, 42.4 mm dia

KATALOGNUMMER

SNSWM10

FUNKTIONER

Ideal for retrofit projects, such as trapeze installations, where disassembly of the support system is not desired


Use as a stopper when installing nVent CADDY Rod Lock assemblies

Can be easily installed, removed, and repositioned at any location along the threaded rod

Ready to use out of the box and eliminates multiple pieces of standard hardware

Functions as a hex nut and flat washer combined

Washer is wide enough to work with standard strut channel profiles



PRODUKTEGENSKABER

Artikelnummer: 390102

Materiale: Stål

Finish: Electrogalvanized

Static Load Safety Factor: 3:1

Rod Size (RS): 10

Diameter (Ø): 42.4 mm

Højde (H): 20mm

Wrench Size: 20 mm



Flange Thickness (FT): 6.5 mm

Static Load: 1557N

YDERLIGERE PRODUKTOPLYSNINGER

For use on plain and electro zinc plated hardware only.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

