


Telescoping box bracket 432–660 mm stud space, 38 mm, 54 mm, 63.5 mm box depth

KATALOGNUMMER

TSGB24



The nVent CADDY Telescoping Screw Gun Box Bracket is a simple and intuitive support for mounting electrical boxes within stud wall applications. This solution delivers traditional mounting, which allows the bracket to bend for multiple depths and install easily with single or multiple electrical boxes. The notched and clearly marked bend points make installation safe, fast and easy.

FUNKTIONER

Designed for both single and multiple box mounting

Unique single-component break-apart design

Stamped inch markings and pilot holes accelerate precise box conduit mounting

Pilot holes allow for easy access with a screwdriver

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly



PRODUKTEGENSKABER

Artikelnummer: 187191

Materiale: Stål

Finish: Pregalvanized

Stud Spacing: 432 - 660 mm

Box Depth: 38mm;54mm;63.5mm

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

