

Internal Strut Beam Clamp with Bolt, Steel, HD, EG, M10 Screw



KATALOGNUMMER

ZT606HDEG

FUNKTIONER

U-shaped clip for clamping the back of strut channel to a beam

Hex bolt included

Requires installation in pairs

PRODUKTEGENSKABER

Artikelnummer: 313270

Materiale: Stål

Finish: Hot-Dip Galvanized;Electrogalvanized

Flange Thickness (FT): 28 mm Max

Width (W): 30 mm


Screw Diameter (Sc): 10

Static Load: 2900N

YDERLIGERE PRODUKTOPLYSNINGER

Static Load is based on one pair of Strut Beam Clamps.

Include strut channel thickness when calculating flange thickness.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

