

Strut Beam Clamp with U-Bolt, Steel, HD, DD Strut



KATALOGNUMMER

ZTA603HD

FUNKTIONER

Complete with U-bolt and nuts

Requires installation in pairs

PRODUKTEGENSKABER

Artikelnummer: 388066

Materiale: Stål

Finish: Hot-Dip Galvanized

Strut Type: DD (124 x 41 mm)

Rod Size (RS): 10

Flange Thickness (FT): 18 mm Max

Width (W): 80 mm

Thickness (T): 6 mm

A: 24 mm

B: 45 mm


C: 180 mm

Static Load: 5000N

YDERLIGERE PRODUKTOPLYSNINGER

Static Load is based on one pair of Strut Beam Clamps.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

