

Strut Beam Clip, S316, 16 mm Max Flange, 13 mm Hole



KATALOGNUMMER

ZTA605S6

FUNKTIONER

Beam Clip for clamping the open side of strut to a beam

Suitable for all strut channels

Requires installation in pairs

Structural attachment to beams to support nVent CADDY Eristrut

FM® Specification Tested

PRODUKTEGENSKABER

Artikelnummer: 387190

Materiale: Stainless Steel 316 (EN 1.4401)

Flange Thickness (FT): 16 mm Max

Hole Size (HS): 13 mm

Length (L): 49mm

Thickness (T): 6 mm



Width (W): 40 mm

Static Load: 2040N

Screw Included: No

YDERLIGERE PRODUKTOPLYSNINGER

Indicated loads are based on installation with 1/2" (M12) hardware and strut channel type A.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

