

EM-P Conduit to Flange Clip



FUNKTIONER

Requires only a hammer to install

Available for EMT, rigid, IMT and aluminum conduit


Will pivot thru 360°

Materiale: Spring Steel
Finish: nVent CADDY Armour



SPECIFIKATIONER

Katalognummer	Artikelnummer	Outer Diameter (OD)	Flange Thickness (FT)	Ultimate Static Load (F)	Certificeringer
12P24	175110	22 - 30 mm	3 - 8 mm	110N	
12P58	175120	22 - 30 mm	8 - 14 mm	110N	
12P912	175130	22 - 30 mm	14 - 20 mm	110N	
16P24	175140	30 - 35 mm	3 - 8 mm	110N	
16P58	175150	30 - 35 mm	8 - 14 mm	110N	
16P912	175160	30 - 35 mm	14 - 20 mm	110N	
8P24	172150	18 - 22 mm	3 - 8 mm	110N	ITB
8P58	172160	18 - 22 mm	8 - 14 mm	110N	ITB
8P912	175100	18 - 22 mm	14 - 20 mm	110N	ITB



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

