

# Four Hole Flat Tee Plate

## FUNKTIONER

Used to create metal frames with nVent CADDY Eristrut channels




## SPECIFIKATIONER

Table 1/2

| Katalognummer | Artikelnummer | Materiale                       | Finish             | Hole Size (HS) | Thickness (T) | A      |
|---------------|---------------|---------------------------------|--------------------|----------------|---------------|--------|
| ZE108         | 313080        | Stål                            | Hot-Dip Galvanized | 14 mm          | 6 mm          | 138 mm |
| ZEA108        | 387580        | Stål                            | Hot-Dip Galvanized | 14 mm          | 6 mm          | 138 mm |
| ZEA108S6      | 388701        | Stainless Steel 316 (EN 1.4401) |                    | 14 mm          | 6 mm          | 138 mm |
| ZEA108EG      | 387581        |                                 | Electrogalvanized  | 14 mm          | 6 mm          | 135 mm |

Table 2/2

| Katalognummer | Artikelnummer | B       | Screw Included | Screw Diameter (Sc) | Screw Length (L) |
|---------------|---------------|---------|----------------|---------------------|------------------|
| ZE108         | 313080        | 90 mm   | Yes            | 10 mm               | 25mm             |
| ZEA108        | 387580        | 90 mm   | No             |                     |                  |
| ZEA108S6      | 388701        | 90 mm   | No             |                     |                  |
| ZEA108EG      | 387581        | 87.5 mm | No             |                     |                  |



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

