


H-PSM Conduit to Flange Clip, Side Mount



FUNKTIONER

Requires only a hammer to install


Available for EMT, rigid and aluminum conduit

Will pivot thru 360°

Orientation: Side Mount
Materiale: Spring Steel
Finish: nVent CADDY Armour

SPECIFIKATIONER

Katalognummer	Artikelnummer	Outer Diameter (OD)	Flange Thickness (FT)	Ultimate Static Load (F)
12P24SM	175220	22 - 30 mm	3 - 8 mm	111N
12P58SM	175230	22 - 30 mm	8 - 14 mm	111N
12P912SM	175240	22 - 30 mm	14 - 20 mm	111N
16P24SM	175260	30 - 35 mm	3 - 8 mm	111N
16P58SM	175270	30 - 35 mm	8 - 14 mm	111N
16P912SM	175280	30 - 35 mm	14 - 20 mm	111N
8P24SM	175180	18 - 22 mm	3 - 8 mm	111N
8P4SM	175170	18 - 22 mm	2 - 3 mm	111N
8P58SM	175190	18 - 22 mm	8 - 14 mm	111N
8P912SM	175200	18 - 22 mm	14 - 20 mm	111N



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

