


Hammer-On Flange Clip, Side Mount

FUNKTIONER

Provides an attachment for wire, S-hooks, chain, nVent CADDY Speed Link or other assemblies to flanges and profiles

Fits most beams

Installs with just a hammer




SPECIFIKATIONER

Katalognummer	Artikelnummer	Materiale	Finish	Flange Thickness (FT)	Hole Size (HS)	Static Load	Certificeringer
2H4	170010	Spring Steel	nVent CADDY Armour	2 - 3 mm	7.1 mm	700N	ITB, UL, cUL
4H1318	170045	Spring Steel	nVent CADDY Armour	21 - 28 mm	7.1 mm	900N	cUL, UL
4H24	170020	Spring Steel	nVent CADDY Armour	3 - 8 mm	7.1 mm	900N	cUL, UL, CE, 4H, EM, EBC, ITB
4H24R5	191018	Spring Steel	nVent CADDY Armour	3 - 8 mm	7.1 mm	900N	CE, 4H, EM, EBC, cUL, UL
4H24S1	179610	Stainless Steel 301 (EN 1.4310)		3 - 8 mm	7.1 mm	650N	
4H24SP25	172320	Spring Steel	nVent CADDY Armour	3 - 8 mm	7.1 mm	900N	CE, 4H, EM, EBC
4H58	170030	Spring Steel	nVent CADDY Armour	8 - 14 mm	7.1 mm	900N	UL, CE, 4H, EM, EBC, cUL, ITB

Katalognummer	Artikelnummer	Materiale	Finish	Flange Thickness (FT)	Hole Size (HS)	Static Load	Certificeringer
4H58R5	191019	Spring Steel	nVent CADDY Armour	8 - 14 mm	7.1 mm	900N	cUL, CE, 4H, EM, EBC, UL
4H58S1	179620	Stainless Steel 301 (EN 1.4310)		8 - 14 mm	7.1 mm	650N	
4H58SP25	172350	Spring Steel	nVent CADDY Armour	8 - 14 mm	7.1 mm	900N	CE, 4H, EM, EBC
4H912	170040	Spring Steel	nVent CADDY Armour	14 - 20 mm	7.1 mm	900N	cUL, UL, CE, 4H, EM, EBC, ITB
4H912R5	191045	Spring Steel	nVent CADDY Armour	14 - 20 mm	7.1 mm	900N	CE, 4H, EM, EBC, cUL, UL
4H912S1	179630	Stainless Steel 301 (EN 1.4310)		14 - 20 mm	7.1 mm	650N	
4H912SP25	172380	Spring Steel	nVent CADDY Armour	14 - 20 mm	7.1 mm	900N	CE, 4H, EM, EBC

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

