


MTVB Gravity Toggle with Rubber Washer

FUNKTIONER

Complete with rod, nut, washer and load distribution block

Threaded rod is secured against unintentional removal

Approved for use in stationary fire protection systems (for pipes up to 2")



Materiale: Stål
Finish: Electrogalvanized




SPECIFIKATIONER

Katalognummer	Artikelnummer	Rod Size (RS)	Length (L)	Drill Bit Diameter	Static Load	Ultimate Static Load (F)	Certificeringer
MTVB10100	584465	10	100mm	25mm	800N	20kN	VdS G412037, FM Approved, Pipe Hanger Components
MTVB10200	584466	10	200mm	25mm	800N	20kN	FM Approved, Pipe Hanger Components
MTVB8100	584455	8	100mm	22mm	800N	20kN	VdS G412037
MTVB8200	584456	8	200mm	22mm	800N	20kN	VdS G412037

YDERLIGERE PRODUKTOPLYSNINGER

Static Load represents the maximum recommended load when fixed to a trapezoidal sheet.

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

