

nVent CADDY Rod Lock Anchor Screw

FUNKTIONER

For use with concrete and solid brick

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position

Works with slightly damaged threads and minor burrs on the threaded rod



Materiale: Stål
Finish: Electrogalvanized




SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Rod Size (RS)	B	C	Length (L)	Drill Bit Diameter
CRLAM10EG	390010	10	32 mm	22 mm	72mm	8mm
CRLAM8EG	390009	8	32 mm	22 mm	72mm	8mm

Table 2/2

Katalognummer	Artikelnummer	Drill Hole Depth	Static Load	Certificeringer
CRLAM10EG	390010	50mm	2900N	FM Approved, Pipe Hanger Components, ITB
CRLAM8EG	390009	50mm	2900N	ITB



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

