

nVent CADDY Speed Link Light Pack with Wedge Anchor



The nVent CADDY Speed Link Light Pack with Wedge Anchor includes a precut length (1m and 2m) of 1mm wire rope riveted to a wedge anchor together with an ultra-low-profile locking device. Contractors can quickly and safely install it to the concrete ceiling to support and secure lighting and signage.

FUNKTIONER

Complete system includes wire, locking device and wedge anchor from fischerwerke GmbH &Co. KG

Quickly and easily attaches into cracked and non-cracked concrete

No special tools required

ETA 06/0175 approval available from fischerwerke GmbH &Co. KG

Static Load Safety Factor: 5:1
Finish: Electrogalvanized
Materiale: Stål;Brass

SPECIFIKATIONER


Table 1/2

Katalognummer	Artikelnummer	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)	Width (W)
CLP1L1WA6	196093	1 mm	1m	54mm	17 mm	12.5 mm
CLP1L2WA6	196094	1 mm	2m	54mm	17 mm	12.5 mm

Table 2/2

Katalognummer	Artikelnummer	Thickness (T)	Angle (a)	Static Load
CLP1L1WA6	196093	6.5 mm	60 °	100N
CLP1L2WA6	196094	6.5 mm	60 °	100N

Drill Bit Diameter: 6mm
Drill Hole Depth: 31mm
Embedment Depth: 25 mm Min



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

