

nVent CADDY Superklip



FUNKTIONER

Closes and locks automatically when the pipe, tube or cable is inserted

One-piece clamp for fast and convenient installation

Fasten with either wood screw, dual threaded screw with or without collar, nail with collar, threaded rod, mounting plate or shot-fire bracket

Materiale: Xenoy®
Temperature: -25 to 90 °C

SPECIFIKATIONER

Katalognummer	Artikelnummer	Outer Diameter (OD)	Copper Tube Size	B	C	Static Load
389001	389001	11.8 - 14.3 mm	3/8"	17.2 mm	29.9 mm	160N
389002	389002	14.3 - 16.8 mm	1/2"	19.5 mm	32 mm	175N
389003	389003	16.8 - 19.5 mm	5/8"	20 mm	35.4 mm	190N
389004	389004	19.5 - 21.8 mm		20 mm	39.4 mm	200N
389005	389005	21.8 - 24.8 mm	3/4"	20 mm	42 mm	215N
389006	389006	24.8 - 27.8 mm		20.2 mm	45.1 mm	240N
389007	389007	27.8 - 31.2 mm	1"	20.2 mm	48.9 mm	260N
389008	389008	31.2 - 35.5 mm	1 1/4"	21 mm	54.4 mm	300N
389009	389009	35.5 - 39.5 mm	1 1/4"	21 mm	59.4 mm	320N
389011	389011	39.5 - 43.5 mm	1 1/2"	21 mm	64.2 mm	360N
389013	389013	50.5 - 55.5 mm	2"	23 mm	78.7 mm	400N
389017	389017	7.8 - 9.5 mm	1/4"	17.1 mm	26.4 mm	135N
389018	389018	9.5 - 11.8 mm	1/4"	17.1 mm	26.4 mm	150N



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

