

PBF Two Hole Base Plate for Threaded Rod

FUNKTIONER

Light duty with two holes and one nut/adaptor



SPECIFIKATIONER

Table 1/2



Katalognummer	Artikelnummer	Materiale	Finish	Rod Size (RS)	Length (L)	Width (W)
PBRM10L120	587160	Stål	Electrogalvanized	10	120mm	40 mm
PBRM10L80	587135	Stål	Electrogalvanized	10	80mm	30 mm
PBRM12L120	587165	Stål	Electrogalvanized	12	120mm	40 mm
PBRM8M10L120	587140	Stål	Electrogalvanized	8, 10	120mm	40 mm
PBRM8M10L70S6	587175	Stainless Steel 316 (EN 1.4401)		8, 10	70mm	33 mm
PBRM8M10L80	587145	Stål	Electrogalvanized	8, 10	80mm	30 mm

Table 2/2

Katalognummer	Artikelnummer	Thickness (T)	A	B	C
PBRM10L120	587160	4 mm	81 mm	18 mm	11 mm

Katalognummer	Artikelnummer	Thickness (T)	A	B	C
PBRM10L80	587135	3 mm	50 mm	18 mm	9 mm
PBRM12L120	587165	4 mm	81 mm	18 mm	11 mm
PBRM8M10L120	587140	4 mm	81 mm	18 mm	11 mm
PBRM8M10L70S6	587175	2 mm	48 mm	10 mm	8 mm
PBRM8M10L80	587145	3 mm	50 mm	18 mm	9 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

