

PEMSA Wire Basket Tray C Bracket



FUNKTIONER

Easy to use, quick connect feature

Ideal for ceiling, wall and channel installations

Side load access for cable installation


IEC 61537 load rating and earthing compliant

Materiale: Stål
Finish: Electrogalvanized



SPECIFIKATIONER

Katalognummer	Artikelnummer	Length 1 (L1)	Length 2 (L2)	Width (W)	Height (H)	Static Load
WBT100CBRKT	820310	137 mm	165 mm	54 mm	190 mm	327N
WBT150CBRKT	820320	137 mm	200 mm	54 mm	190 mm	353N
WBT200CBRKT	820330	137 mm	265 mm	54 mm	190 mm	284N
WBT300CBRKT	820340	137 mm	365 mm	54 mm	190 mm	245N
WBT400CBRKT	820350	137 mm	465 mm	54 mm	190 mm	177N



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

