


PEMSA Wire Basket Tray Center Support



FUNKTIONER

Ideal for tray widths up to 200mm

Side load access for cable installation


IEC 61537 load rating and earthing compliant

Materiale: Stål
Finish: Electrogalvanized



SPECIFIKATIONER

Katalognummer	Artikelnummer	Farve	Length (L)	Width (W)	Height (H)	Hole Size (HS)	Certificeringer
WBTCTRSPRTM10	820420		59mm	35 mm	5 mm	8 - 10 mm	CE, CADDY EU WBT QC, ANOR EU WTB EG S4 BG
WBTCTRSPRTM10BG	820421	Black	59mm	35 mm	5 mm	8 - 10 mm	ANOR EU WTB EG S4 BG, CE, CADDY EU WBT QC
WBTCTRSPRTM6	820400		59mm	35 mm	5 mm	6 mm	CE, CADDY EU WBT QC



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

