

# PEMSA Wire Basket Tray Quick Splice Bar



## FUNKTIONER

Easy to use, quick connect feature

No additional hardware

Works with wide range of tray sizes and configurations


IEC 61537 load rating and earthing compliant

**Materiale:** Stål  
**Finish:** Electrogalvanized



## SPECIFIKATIONER

| Katalognummer | Artikelnummer | Farve | Length (L) | Width (W) | Height (H) | Hole Size (HS) |
|---------------|---------------|-------|------------|-----------|------------|----------------|
| WBTQBARBG     | 820706        | Black | 240.5mm    | 24 mm     | 16.5 mm    | 5 mm           |
| WBTQBAREG     | 820711        |       | 240.5mm    | 24 mm     | 16.5 mm    | 5 mm           |



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

