

SC Cable Snap Clip



FUNKTIONER

Easily supports cable and plastic conduit from flanges

Requires only a hammer to install

Materiale: Spring Steel
Finish: nVent CADDY Armour

SPECIFIKATIONER


Table 1/2

Katalognummer	Artikelnummer	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
24SC1011	187550	2 - 4 mm	10 - 11 mm	0.6 mm
24SC1214	187570	2 - 4 mm	12 - 14 mm	0.6 mm
24SC1518	187590	2 - 4 mm	15 - 18 mm	0.6 mm
24SC1518R25	191003	2 - 4 mm	15 - 18 mm	0.6 mm
24SC1924	187610	2 - 4 mm	19 - 24 mm	0.6 mm
24SC1924R25	191004	2 - 4 mm	19 - 24 mm	0.6 mm
24SC2530	187630	2 - 4 mm	25 - 30 mm	0.6 mm
24SC2530R25	191005	2 - 4 mm	25 - 30 mm	0.6 mm
24SC67	187510	2 - 4 mm	6 - 7 mm	0.6 mm
24SC78	187710	2 - 4 mm	7 - 8 mm	0.6 mm
24SC89	187530	2 - 4 mm	8 - 9 mm	0.6 mm
24SC910	187750	2 - 4 mm	9 - 10 mm	0.6 mm

Katalognummer	Artikelnummer	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
47SC1011	187540	4 - 7 mm	10 - 11 mm	0.6 mm
47SC1214	187560	4 - 7 mm	12 - 14 mm	0.6 mm
47SC1518	187580	4 - 7 mm	15 - 18 mm	0.6 mm
47SC1518R25	191009	4 - 7 mm	15 - 18 mm	0.6 mm
47SC1924	187600	4 - 7 mm	19 - 24 mm	0.6 mm
47SC1924R25	191010	4 - 7 mm	19 - 24 mm	0.6 mm
47SC2530	187620	4 - 7 mm	25 - 30 mm	0.6 mm
47SC2530R25	191011	4 - 7 mm	25 - 30 mm	0.6 mm

Table 2/2

Katalognummer	Artikelnummer	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
47SC67	187500	4 - 7 mm	6 - 7 mm	0.6 mm
47SC78	187720	4 - 7 mm	7 - 8 mm	0.6 mm
47SC89	187520	4 - 7 mm	8 - 9 mm	0.6 mm
47SC910	187760	4 - 7 mm	9 - 10 mm	0.6 mm
812SC1011	187660	8 - 12 mm	10 - 11 mm	0.6 mm
812SC1214	187670	8 - 12 mm	12 - 14 mm	0.6 mm
812SC1518	187680	8 - 12 mm	15 - 18 mm	0.6 mm
812SC1518R25	191015	8 - 12 mm	15 - 18 mm	0.6 mm
812SC1924	187690	8 - 12 mm	19 - 24 mm	0.6 mm
812SC1924R25	191016	8 - 12 mm	19 - 24 mm	0.6 mm
812SC2530	187700	8 - 12 mm	25 - 30 mm	0.6 mm
812SC2530R25	191017	8 - 12 mm	25 - 30 mm	0.6 mm
812SC67	187640	8 - 12 mm	6 - 7 mm	0.6 mm
812SC78	187730	8 - 12 mm	7 - 8 mm	0.6 mm
812SC89	187650	8 - 12 mm	8 - 9 mm	0.6 mm
812SC910	187770	8 - 12 mm	9 - 10 mm	0.6 mm



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

