


Speedway Cable Ladder Equal Tee



FUNKTIONER

Creates a quick and easy equal tee pathway intersection

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic

Materiale: Stål
Finish: Hot-Dip Galvanized



SPECIFIKATIONER

Table 1/2


Katalognummer	Artikelnummer	Width (W)	Angle (a)	A	B	C
CL110X150ETHD	840700	150 mm	90 °	900 mm	450 mm	950 mm
CL110X300ETHD	840710	300 mm	90 °	900 mm	525 mm	950 mm
CL110X450ETHD	840720	450 mm	90 °	900 mm	600 mm	950 mm
CL110X600ETHD	840730	600 mm	90 °	900 mm	675 mm	950 mm
CL110X750ETHD	840740	750 mm	90 °	900 mm	750 mm	950 mm
CL110X900ETHD	840750	900 mm	90 °	900 mm	825 mm	950 mm

Table 2/2

Katalognummer	Artikelnummer	D	E
CL110X150ETHD	840700	80 mm	110 mm
CL110X300ETHD	840710	80 mm	110 mm
CL110X450ETHD	840720	80 mm	110 mm
CL110X600ETHD	840730	80 mm	110 mm

Katalognummer	Artikelnummer	D	E
CL110X750ETHD	840740	80 mm	110 mm
CL110X900ETHD	840750	80 mm	110 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

