

Strut Nut without Spring

FUNKTIONER

Used to create metal frames with nVent CADDY Eristrut channels





Static Load Safety Factor: 3:1

SPECIFIKATIONER

Katalognummer	Artikelnummer	Materiale	Finish	Rod Size (RS)	Thickness (T)	Torque (TQ)
NUTM10EG	315025	Stål	Electrogalvanized	10	8 mm	55 N·m
NUTM10HD	315020	Stål	Hot-Dip Galvanized	10	8 mm	55 N·m
NUTM10S6	315160	Stainless Steel 316 (EN 1.4401)		10	8 mm	55 N·m
NUTM12EG	315035	Stål	Electrogalvanized	12	8 mm	55 N·m
NUTM12HD	315030	Stål	Hot-Dip Galvanized	12	8 mm	55 N·m
NUTM12S6	315170	Stainless Steel 316 (EN 1.4401)		12	8 mm	55 N·m
NUTM16EG	315036	Stål	Electrogalvanized	16	11.7 mm	125 N·m
NUTM16HD	315037	Stål	Hot-Dip Galvanized	16	11.7 mm	125 N·m

Katalognummer	Artikelnummer	Materiale	Finish	Rod Size (RS)	Thickness (T)	Torque (TQ)
NUTM6EG	314995	Stål	Electrogalvanized	6	6 mm	12 N·m
NUTM6HD	315000	Stål	Hot-Dip Galvanized	6	6 mm	12 N·m
NUTM6S6	315140	Stainless Steel 316 (EN 1.4401)		6	6 mm	12 N·m
NUTM8EG	315015	Stål	Electrogalvanized	8	6 mm	28 N·m
NUTM8HD	315010	Stål	Hot-Dip Galvanized	8	6 mm	28 N·m
NUTM8S6	315150	Stainless Steel 316 (EN 1.4401)		8	6 mm	28 N·m

Pull-Out Strength				
Part Number	Channel Type	Channel Thickness		
		2,5 mm	2 mm	1,5 mm
NUTM6xx	A, C	2000 N	2000 N	2000 N
	D, E	2000 N	-	-
NUTM8xx	A, C	3330 N	3330 N	3330 N
	D, E	3330 N	-	-
NUTM10xx	A, C	4890 N	4440 N	4440 N
	D, E	4890 N	-	-
NUTM12xx	A, C	4890 N	4660 N	4440 N
	D, E	3670 N	-	-
NUTM12Txx	A	5670 N	5050 N	4440 N
	D, E	4250 N	-	-
NUTM16xx	A	5670 N	4660 N	4440 N
	D, E	4250 N	-	-



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

