


Wire Basket Tray C Bracket



Engineered for efficiency and adaptability, the nVent CADDY Wire Basket Tray C Bracket is a fast and simple component of modern cable management systems. Designed to streamline installation processes, this bracket excels in both hard-ceiling and two-tier wall mounting scenarios, offering contractors a reliable and time-saving solution for complex environments

The C Bracket ensures that high-performance, low-voltage and data cables are securely supported with minimal effort. Simply pair with the nVent CADDY Wire Basket Tray Washer Support or nVent CADDY Wire Basket Tray Ground Splice and quickly fasten it to the wire basket tray to create a robust framework for layered tray runs. This combination not only enhances structural integrity but also provides the flexibility needed for multi-tiered installations, accommodating evolving infrastructure demands without compromising safety or performance.

FUNKTIONER

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Side load access for cable installation

Ideal for ceiling, wall and channel installations

Side load access for simple cable installation

Materiale: Stål
Finish: Electrogalvanized





SPECIFIKATIONER

Katalognummer	Farve	Height (H)	Width (W)	Length (L)	Length 1 (L1)	Hole Size (HS)	Unit Weight
WBTCBRKT12		200.03 mm	41.4 mm	350.52mm	139.7 mm	7.137 mm	1.025 kg
WBTCBRKT12BA	Black	200.03 mm	41.4 mm	350.52mm	139.7 mm	7.137 mm	1.025 kg
WBTCBRKT18		200.03 mm	41.4 mm	499.11mm	139.7 mm	7.137 mm	1.27 kg
WBTCBRKT18BA	Black	200.03 mm	41.4 mm	499.11mm	139.7 mm	7.137 mm	1.27 kg
WBTCBRKT4		200.03 mm	41.4 mm	151.917mm	139.7 mm	7.137 mm	0.708 kg

Katalognummer	Farve	Height (H)	Width (W)	Length (L)	Length 1 (L1)	Hole Size (HS)	Unit Weight
WBTCBRKT4BA	Black	200.03 mm	41.4 mm	151.917mm	139.7 mm	7.137 mm	0.708 kg
WBTCBRKT6		200.03 mm	41.4 mm	201.93mm	139.7 mm	7.137 mm	0.789 kg
WBTCBRKT6BA	Black	200.03 mm	41.4 mm	201.93mm	139.7 mm	7.137 mm	0.789 kg
WBTCBRKT8		200.03 mm	41.4 mm	251.46mm	139.7 mm	7.137 mm	0.866 kg
WBTCBRKT8BA	Black	200.03 mm	41.4 mm	251.46mm	139.7 mm	7.137 mm	0.866 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

