

# Wire Basket Tray Center Support



The nVent CADDY Wire Basket Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

## FUNKTIONER

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod


**Materiale:** Stål  
**Finish:** Electrogalvanized



## SPECIFIKATIONER

| Katalognummer | Farve | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Unit Weight |
|---------------|-------|------------|-----------|------------|----------------|-------------|
| WBTCTSPRT12   |       | 193.55 mm  | 41.4 mm   | 292.176mm  | 15.75 mm       | 1.225 kg    |
| WBTCTSPRT4    |       | 193.55 mm  | 41.4 mm   | 105.156mm  | 15.75 mm       | 0.7 kg      |
| WBTCTSPRT4BA  | Black | 193.55 mm  | 41.4 mm   | 105.156mm  | 15.75 mm       | 0.7 kg      |
| WBTCTSPRT6    |       | 193.55 mm  | 41.4 mm   | 147.777mm  | 15.75 mm       | 0.816 kg    |
| WBTCTSPRT8    |       | 193.55 mm  | 41.4 mm   | 190.551mm  | 15.75 mm       | 0.907 kg    |

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDDT](http://nVent.com/ENDDT)

