

Wire Basket Tray Independent Underfloor Support



The nVent CADDY Wire Basket Tray Underfloor Support provides a reliable method for routing wire basket trays beneath the floor with independent structural support. This component is ideal for installations requiring low-voltage cabling to pass under cabinets or equipment.

Engineered for stability and simplicity, the underfloor support system eliminates the need for complex framing. It braces the tray directly beneath raised floors, allowing for clean, unobtrusive cable pathways that preserve floor space and reduce visual clutter. This is especially valuable in data centers, control rooms, and other high-density environments where cable organization and accessibility are critical.

The Support integrates seamlessly with the broader nVent CADDY Wire Basket Tray System, ensuring compatibility with shaped and round wire tray profiles. Its design accommodates standard fasteners and finishes, including pre-galvanized, zinc electroplate, and powder coat options, making it adaptable to a wide range of project specifications.

FUNKTIONER

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Maintains a fixed and secure distance from the ground to ensure safety and accessibility

Available in a range of sizes to match wire basket tray design

Fixed height ensures a level installation


Materiale: Stål
Finish: Pregalvanized

SPECIFIKATIONER

Katalognummer	Height (H)	Length (L)	Length 1 (L1)	Width (W)	Hole Size (HS)	Unit Weight
WBTUS04	32 mm	767mm	560.78 mm	235 mm	14.3 mm	0.862 kg
WBTUS06	32 mm	868mm	560.78 mm	235 mm	14.3 mm	0.953 kg
WBTUS08	32 mm	965mm	560.78 mm	235 mm	14.3 mm	1.089 kg
WBTUS12	32 mm	1174mm	560.78 mm	235 mm	14.3 mm	1.588 kg
WBTUS18	32 mm	1474mm	560.78 mm	235 mm	14.3 mm	2.404 kg

Katalognummer	Height (H)	Length (L)	Length 1 (L1)	Width (W)	Hole Size (HS)	Unit Weight
WBTUS24	32 mm	1778mm	560.78 mm	235 mm	14.3 mm	3.22 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

