


# Wire Basket Tray PreForm Elbow 90°



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## FUNKTIONER

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Materiale:** Stål  
**Finish:** Pregalvanized;Polyurethane



## SPECIFIKATIONER

Table 1/2


| Katalognummer | Farve | Height (H) | Width (W)  | Length (L) | Hole Size (HS) | Radius (R) |
|---------------|-------|------------|------------|------------|----------------|------------|
| WBTR902X12    |       | 50.8 mm    | 515.62 mm  | 515.62mm   | 19.05 mm       | 94.64mm    |
| WBTR902X12BA  | Black | 50.8 mm    | 515.62 mm  | 515.62mm   | 19.05 mm       | 94.64mm    |
| WBTR902X18    |       | 50.8 mm    | 665.734 mm | 665.734mm  | 19.05 mm       | 94.64mm    |
| WBTR902X18BA  | Black | 50.8 mm    | 665.734 mm | 665.734mm  | 19.05 mm       | 94.64mm    |
| WBTR902X24    |       | 50.8 mm    | 817.88 mm  | 817.88mm   | 19.05 mm       | 94.64mm    |
| WBTR902X24BA  | Black | 50.8 mm    | 817.88 mm  | 817.88mm   | 19.05 mm       | 94.64mm    |
| WBTR902X4     |       | 50.8 mm    | 317.7 mm   | 317.7mm    |                | 94.64mm    |
| WBTR902X4BA   | Black | 50.8 mm    | 317.7 mm   | 317.7mm    |                | 94.64mm    |
| WBTR902X6     |       | 50.8 mm    | 365.76 mm  | 365.76mm   |                | 94.64mm    |

| Katalognummer | Farve | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) |
|---------------|-------|------------|-----------|------------|----------------|------------|
| WBTR902X6BA   | Black | 50.8 mm    | 365.76 mm | 365.76mm   |                | 94.64mm    |
| WBTR902X8     |       | 50.8 mm    | 416.56 mm | 416.56mm   |                | 94.64mm    |
| WBTR902X8BA   | Black | 50.8 mm    | 416.56 mm | 416.56mm   |                | 94.64mm    |

Table 2/2

| Katalognummer | Unit Weight | Certificeringer                                  |
|---------------|-------------|--------------------------------------------------|
| WBTR902X12    | 1.814 kg    | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X12BA  | 1.814 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X18    | 3.175 kg    | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X18BA  | 3.175 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X24    | 4.99 kg     | cUL, UL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X24BA  | 4.99 kg     | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X4     | 0.454 kg    | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTR902X4BA   | 0.454 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X6     | 0.907 kg    | CE, nVent CADDY Wire Basket Tray System, cUL, UL |
| WBTR902X6BA   | 0.907 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTR902X8     | 0.907 kg    | UL, cUL, CE, nVent CADDY Wire Basket Tray System |
| WBTR902X8BA   | 0.907 kg    | CE, nVent CADDY Wire Basket Tray System          |

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

