


Wire Basket Tray, Round Wire



The nVent CADDY Wire Basket Tray, Round Wire is a continuous pathway solution to support high-performance cabling systems while providing an ideal foundation for datacom and electrical contractors.

FUNKTIONER

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fiber optic

UL Classified as an equipment ground conductor, no field removal of paint required

T-Weld edge wire for cable and installer protection

Mill Certificates are available to document recycled content for possible LEED credits/certification



SPECIFIKATIONER

Table 1/3

Katalognummer	Materiale	Finish	Farve	Height (H)	Width (W)	Length (L)
WBT2X12	Stål	Pregalvanized		50 mm	300	3000mm
WBT2X12BA	Stål	Pregalvanized	Black	50 mm	300	3000mm
WBT2X12EG	Stål	Electrogalvanized		50 mm	300	3000mm
WBT2X18	Stål	Pregalvanized		50 mm	450	3000mm
WBT2X18BA	Stål	Pregalvanized	Black	50 mm	450	3000mm
WBT2X18EG	Stål	Pregalvanized		50 mm	450	3000mm
WBT2X24	Stål	Pregalvanized		50 mm	600	3000mm
WBT2X24BA	Stål	Pregalvanized	Black	50 mm	600	3000mm
WBT2X24EG	Stål	Pregalvanized		50 mm	600	3000mm
WBT2X4	Stål	Pregalvanized		50 mm	100	3000mm
WBT2X4BA	Stål	Pregalvanized	Black	50 mm	100	3000mm

Katalognummer	Materiale	Finish	Farve	Height (H)	Width (W)	Length (L)
WBT2X4EG	Stål	Pregalvanized		50 mm	100	3000mm
WBT2X6	Stål	Pregalvanized		50 mm	150	3000mm
WBT2X6BA	Stål	Pregalvanized	Black	50 mm	150	3000mm
WBT2X6EG	Stål	Electrogalvanized		50 mm	150	3000mm
WBT2X8	Stål	Pregalvanized		50 mm	200	3000mm
WBT2X8BA	Stål	Pregalvanized	Black	50 mm	200	3000mm
WBT2X8EG	Stål	Electrogalvanized		50 mm	200	3000mm
WBT4X12	Stål	Pregalvanized		100 mm	300	3000mm
WBT4X12BA	Stål	Pregalvanized	Black	100 mm	300	3000mm

Table 2/3

Katalognummer	Materiale	Finish	Farve	Height (H)	Width (W)	Length (L)
WBT4X12EG	Stål	Electrogalvanized		100 mm	300	3000mm
WBT4X18	Stål	Pregalvanized		100 mm	450	3000mm
WBT4X18BA	Stål	Pregalvanized	Black	100 mm	450	3000mm
WBT4X18EG	Stål	Electrogalvanized		100 mm	450	3000mm
WBT4X24	Stål	Pregalvanized		100 mm	600	3000mm
WBT4X24BA	Stål	Pregalvanized	Black	100 mm	600	3000mm
WBT4X24EG	Stål	Electrogalvanized		100 mm	600	3000mm
WBT4X4	Stål	Pregalvanized		100 mm	100	3000mm
WBT4X4BA	Stål	Pregalvanized	Black	100 mm	100	3000mm
WBT4X4EG	Stål	Electrogalvanized		100 mm	100	3000mm
WBT4X6	Stål	Pregalvanized		100 mm	150	3000mm
WBT4X6BA	Stål	Pregalvanized	Black	100 mm	150	3000mm
WBT4X6EG	Stål	Electrogalvanized		100 mm	150	3000mm
WBT6X12	Stål	Pregalvanized		150 mm	300	3000mm
WBT6X12BA	Stål	Pregalvanized	Black	150 mm	300	3000mm
WBT6X12EG	Stål	Electrogalvanized		150 mm	300	3000mm
WBT6X18	Stål	Pregalvanized		150 mm	450	3000mm
WBT6X18BA	Stål	Pregalvanized	Black	150 mm	450	3000mm
WBT6X18EG	Stål	Pregalvanized		150 mm	450	3000mm
WBT6X24	Stål	Pregalvanized		150 mm	600	3000mm

Table 3/3

Katalognummer	Materiale	Finish	Farve	Height (H)	Width (W)	Length (L)
WBT6X24BA	Stål	Pregalvanized	Black	150 mm	600	3000mm

Katalognummer	Materiale	Finish	Farve	Height (H)	Width (W)	Length (L)
WBT6X24EG	Stål	Electrogalvanized		150 mm	600	3000mm

Table 1/3

Katalognummer	Unit Weight	Certificeringer
WBT2X12	6.35 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X12BA	6.35 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X12EG	6.35 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X18	8.618 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X18BA	8.618 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X18EG	8.618 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X24	10.886 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X24BA	10.886 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X24EG	10.886 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X4	3.629 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X4BA	3.629 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X4EG	3.629 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X6	4.082 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X6BA	4.082 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X6EG	4.082 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X8	4.436 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT2X8BA	4.535 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT2X8EG	4.535 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT4X12	8.165 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT4X12BA	8.165 kg	UL, CE, nVent CADDY Wire Basket Tray System

Table 2/3



Katalognummer	Unit Weight	Certificeringer
WBT4X12EG	8.165 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT4X18	10.433 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT4X18BA	10.433 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT4X18EG	10.433 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT4X24	13.154 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT4X24BA	13.154 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT4X24EG	13.154 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT4X4	4.536 kg	UL, CE, nVent CADDY Wire Basket Tray System

Katalognummer	Unit Weight	Certificeringer
WBT4X4BA	4.536 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT4X4EG	4.536 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT4X6	4.99 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT4X6BA	4.99 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT4X6EG	4.99 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT6X12	9.979 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT6X12BA	9.979 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT6X12EG	9.979 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT6X18	11.34 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT6X18BA	11.34 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT6X18EG	11.34 kg	CE, nVent CADDY Wire Basket Tray System, UL
WBT6X24	14.515 kg	UL, CE, nVent CADDY Wire Basket Tray System

Table 3/3

Katalognummer	Unit Weight	Certificeringer
WBT6X24BA	14.515 kg	UL, CE, nVent CADDY Wire Basket Tray System
WBT6X24EG	9.979 kg	UL, CE, nVent CADDY Wire Basket Tray System

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

