

# nVent ERICO Ericore Unterminated Conductor



## FUNKTIONER

Low-inductance, low-impedance cable designed to minimize voltage build-up due to lightning impulses

Multiple insulated layers of conductor reduce the potential of side flashing

Requires upper and lower termination kits

## SPECIFIKATIONER

Table 1/3

| Katalognummer | Artikelnummer | Length (L) | Length | Length (L) | Length | Capacitance |
|---------------|---------------|------------|--------|------------|--------|-------------|
| ERICORE       | 701875        | 1m         | 1 m    | 1m         | 1 m    | 0.75 nF     |

Table 2/3

| Katalognummer | Artikelnummer | Cross Section     | Cross Section     | Diameter (Ø) | Impedance | Inductance |
|---------------|---------------|-------------------|-------------------|--------------|-----------|------------|
| ERICORE       | 701875        | 50mm <sup>2</sup> | 50mm <sup>2</sup> | 36 mm        | 12 Ω Max  | 37nH       |


Table 3/3

| Katalognummer | Artikelnummer | Resistance (Rdc) | Resistance (Rimp) | Unit Weight |
|---------------|---------------|------------------|-------------------|-------------|
| ERICORE       | 701875        | 0.5mΩ·m          | 6mΩ·m             | 1.18 kg     |

## YDERLIGERE PRODUKTOPLYSNINGER

Consult nVent ERICO technical support or the installation manual for guidance on maximum allowable lengths.

Inductance and Capacitance are per meter.



## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

