

Kabelklemmer, CAC

Kabelklemmerne holder kablerne på plads og fjerner eventuelle ydre belastninger, hvilket medvirker til at forhindre beskadigelse af udstyret.


FUNKTIONER

Beskrivelse: Til fastgørelse af indgående kabler på CAB- og CABP-montageskiner. Holder kablet på plads og understøtter vægten.

Materiale: Forzinket stål.

Pakke størrelse: 25 klemmer.

Monteringskrav: Tilføj CAB/CABP for at montere kabelklemmerne CAC.



Materiale: Lakeret Stål
Finish: Forzinket Stål
Tykkelse: 2mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Enclosure Material	Produktfamilie	Cable Diameter Range
CAC0612	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	6 – 12mm
CAC1014	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	10 – 14mm
CAC1216	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	12 – 16mm
CAC1418	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	14 – 18mm
CAC1822	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	18 – 22mm
CAC2226	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	22 – 26mm
CAC2630	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	26 – 30mm
CAC3034	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	30 – 34mm
CAC3438	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	34 – 38mm
CAC3842	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	38 – 42mm
CAC4246	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	42 – 46mm
CAC5864	64mm	25mm	19mm	Lakeret Stål, Stainless Steel	Free-Standing	58 – 64mm

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.