

Dør til kabelrum | Gulvskabe, DPA

Kabelføringsdøren giver adgang til enkelte kabelrum, og gør det dermed nemt at montere og vedligeholde komponenter i marken.



FUNKTIONER

Beskrivelse: Lukker en lodret kabelsektion. Bruges i kombination med CDV. Brug DPC/DPCV for at lukke front-, top- og bundpaneler.

Materiale: 2 mm stålplade.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedsgard: Beskyttelsesklasse IP 44.

Monteringskrav: Tilføj CDH for MC rammer og brug CDHK for MK rammer.

Pakke størrelse: 1 dør med hængsler og udstyret med dobbelt-bit 3 mm espagnolet-låsesystem.

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Enclosure Material	Produktfamilie	Materiale	Finish
DPA1404R5	1400mm	400mm	Lakeret Stål	Free-Standing	Lakeret Stål	Plated
DPA1604R5	1600mm	400mm	Lakeret Stål	Free-Standing	Lakeret Stål	Plated
DPA1606R5	1600mm	600mm	Lakeret Stål	Free-Standing	Lakeret Stål	Plated
DPA1804R5	1800mm	400mm	Lakeret Stål	Free-Standing	Lakeret Stål	Plated
DPA1806R5	1800mm	600mm	Lakeret Stål	Free-Standing	Lakeret Stål	Plated
DPA2004R5	2000mm	400mm	Lakeret Stål	Free-Standing	Lakeret Stål	Plated
DPA2006R5	2000mm	600mm	Lakeret Stål	Free-Standing	Lakeret Stål	Plated

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.