


Klik-i profil | Gulvskabe, CLPK



Ekstra tilbehør og elektrisk udstyr kan monteres hurtigt og nemt på de ønskede steder ved at bruge disse klik-monteringsprofiler.

FUNKTIONER

Beskrivelse: Universal profil for tilpasning både i dybden og bredden på 25 mm DIN hulmønsteret i skabsrammen eller i kombination med CLPF- og VB-profilerne. Den 75 mm brede profil er udstyret med tre rækker huller, hvoraf den ene er drejet 90 grader. Det gør det muligt at montere CLPF-profiler i begge retninger. CLPK kan sikres med selvskærende skruer.

Materiale: 1,5 mm forzinket stål.

Pakke størrelse: 4 profiler.

Materiale: Lakeret Stål
Finish: Forzinket Stål
Tykkelse: 1.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Load Rating	Enclosure Material
CLPK1000	74mm	1000mm	26mm	1200N	Lakeret Stål
CLPK1200	74mm	1200mm	26mm	1200N	Lakeret Stål
CLPK300	74mm	300mm	26mm	2000N	Lakeret Stål
CLPK400	74mm	400mm	26mm	2000N	Lakeret Stål
CLPK500	74mm	500mm	26mm	2000N	Lakeret Stål
CLPK600	74mm	600mm	26mm	1600N	Lakeret Stål
CLPK800	74mm	800mm	26mm	1600N	Lakeret Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.