


Cool Vægstativ Sort, DCHL-B



nVent Data Solutions Wall-of-Cool Rack er en modulær støttestruktur, der er designet til at implementere og idriftsætte bagdørskølere med fuld kapacitet uden at være afhængig af en bygningsstruktur for stabilitet. The permanent structure allows for networking cabinets to be rolled directly up to rack and secured with a clamp for easy rack-and-roll positioning.

FUNKTIONER

10-gauge ramme i lakeret stål, svejset konstruktion med 12-gauge indvendig flange i lakeret stål.

Simple installation to allow for single person install. Designet til at blive forankret til gulvet for selvforsyning.

Monteringspunkter tilgængelige til understøttelse af køreledningsbane.

Gangable features to support a complete fan wall design for rack and roll deployments.

Integrates directly with standard nVent RDHX Pro without any modificaitons as well as other 3rd party rack manufacturers.

Proven UL stability rated solution to ensure safety.

Kompatibel med top- og bundfremføringsapplikationer med en hævet gulvslangeindtrængning.

Overfladerne omfatter RAL9005 (sort).

SPECIFIKATIONER

Katalognummer	Product Type	Produktfamilie	Bredde	Dybde	Højde	Beskyttelsesgrad
DWC42U600B	Air/Liquid Heat Exchanger	Cooling	600mm	368mm	2046mm	UL2416
DWC42U750B	Air/Liquid Heat Exchanger	Cooling	750mm	368mm	2046mm	UL2416
DWC42U800B	Air/Liquid Heat Exchanger	Cooling	800mm	368mm	2046mm	UL2416
DWC48U600B	Air/Liquid Heat Exchanger	Cooling	600mm	368mm	2313mm	UL2416
DWC48U750B	Air/Liquid Heat Exchanger	Cooling	750mm	368mm	2313mm	UL2416
DWC48U800B	Air/Liquid Heat Exchanger	Cooling	800mm	368mm	2313mm	UL2416

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl,

materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.