


LED-skabsbelysning 24 V, EL1200D24V

LED-skabslys er specielt konstrueret til nVent HOFFMAN-skabe. Værktøjsfri montering reducerer monteringsiden. Enkel plug-and-play-kabelføring. 24V (DC) model.



FUNKTIONER

Beskrivelse: LED-skabslys er specielt konstrueret til nVent HOFFMAN-skabe. Hurtig og værktøjsfri montering takket være et låsekrogssystem, som passer til 25 mm hulmønsteret på nVent HOFFMAN-skabe. Kan monteres vandret eller lodret.

Please be advised that when using the clamp mechanism to mount these lights, they cannot be installed on the top rail of ProLine and ProLine G2 cabinet frames.

Materiale:	Plastik
Finish:	Smooth
Farve:	Black
Lampetype:	LED
Farvetemperatur:	4000K
Lysfarve:	Neutral White
Driftstemperatur:	-20 to 55°C

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Stiktype	Light Output	Power
EL1200D24V	76mm	315mm	48mm	NA	1200lm	12W
EL1200DS	76mm	364mm	48mm	SCHUKO, Type F	1200lm	12W
EL1200DS-BF	76mm	364mm	48mm	Type E	1200lm	12W
EL1200DS-CH	76mm	364mm	48mm	Type J	1200lm	12W
EL1200DS-GB	76mm	364mm	48mm	Type G	1200lm	12W
EL1200DS-US	76mm	364mm	48mm	Type B	1200lm	12W
EL1200M	76mm	315mm	48mm	NA	1200lm	12W
EL1200M24V	76mm	315mm	48mm	NA	1200lm	12W
EL1200MS	76mm	364mm	48mm	SCHUKO, Type F	1200lm	12W
EL1200MS-BF	76mm	364mm	48mm	Type E	1200lm	12W
EL1200MS-CH	76mm	364mm	48mm	Type J	1200lm	12W

Katalognummer	Højde	Bredde	Dybde	Stiktype	Light Output	Power
EL1200MS-GB	76mm	364mm	48mm	Type G	1200lm	12W
EL1200MS-US	76mm	364mm	48mm	Type B	1200lm	12W
EL900D	76mm	314mm	48mm	NA	900lm	9W
EL900DS	76mm	364mm	48mm	SCHUKO, Type F	900lm	9W
EL900DS-BF	76mm	364mm	48mm	Type E	900lm	9W
EL900DS-CH	76mm	364mm	48mm	Type J	900lm	9W
EL900DS-GB	76mm	364mm	48mm	Type G	900lm	9W
EL900DS-US	76mm	364mm	48mm	Type B	900lm	9W

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.