


Front/bag bundrammer | Gulvskabe, PCU



Denne ramme skaber ekstra plads i bunden og kan adskilles fra resten af skabet. Den er udstyret med universalhulmønster for nem montering af tilbehør.

FUNKTIONER

Beskrivelse: Til montering og føring af kabler eller montering af samleskiner. Hulmønster identisk med skabsrammen gør det muligt at montere alt relevant tilbehør (f.eks. CLPF, CLPK, osv.). Monteret i skabets bund med M12-skruer (medleveres). Standardhøjde 300 mm (200 mm leveres kun efter anmodning).

Materiale: Ramme i 1,75 mm stålplade, paneler i 1,35 mm stålplade.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedsgrad: IP 41 | TYPE 1.

Monteringskrav: Benyt PCUP sidepaneler for lukning af siderne.

Pakke størrelse: 1 stk. med front- og bagplader med monteringsmateriale.

Materiale: Stål
Finish: Plated
Farve: Light Gray
Farvekode: RAL 7035

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Enclosure Material
PCU3046R5	300mm	400mm	600mm	Stainless Steel
PCU3048R5	300mm	400mm	800mm	Stainless Steel
PCU3066R5	300mm	599mm	600mm	Stainless Steel

Katalognummer	Højde	Bredde	Dybde	Enclosure Material
PCU3068R5	300mm	599mm	800mm	Stainless Steel
PCU3086R5	300mm	800mm	600mm	Stainless Steel
PCU3088R5	300mm	800mm	800mm	Stainless Steel
PCU3106R5	300mm	999mm	600mm	Stainless Steel
PCU3108R5	300mm	999mm	800mm	Stainless Steel
PCU3126R5	300mm	1199mm	600mm	Stainless Steel
PCU3128R5	300mm	1199mm	800mm	Stainless Steel
PCU2046R5	200mm	400mm	600mm	Stainless Steel
PCU2048R5	200mm	400mm	800mm	Stainless Steel
PCU2066R5	200mm	599mm	600mm	Stainless Steel
PCU2068R5	200mm	599mm	800mm	Stainless Steel
PCU2086R5	200mm	800mm	600mm	Stainless Steel
PCU2088R5	200mm	800mm	800mm	Stainless Steel
PCU2106R5	200mm	999mm	600mm	Stainless Steel
PCU2108R5	200mm	999mm	800mm	Stainless Steel
PCU2126R5	200mm	1199mm	600mm	Stainless Steel
PCU2128R5	200mm	1199mm	800mm	Stainless Steel

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.