

Glasdøre, ADCS



De elektriske komponenter kan ses, når døren er lukket, hvilket holder uautoriseret personale ude og opretholder beskyttelsen mod indtrængning.

FUNKTIONER

Beskrivelse: Til erstatning for standarddøren. Tydelig visning de komponenter, som er installeret inde i skabet. Anvendes med tilbehør fra låseprogrammet.

Materiale: 1.5 mm AISI 304 rustfrit stål. 2 mm til skabe med en højde eller bredde på 600 mm eller derover, 4 mm klart sikkerhedsglas.

Overfladebehandling: 400 slebet rustfrit stål.

Tæthedsgrad: Er i overensstemmelse med IP 55 | TYPE 12, 13, IK 07.

Pakke størrelse: 1 stk. dør.

The glazed door allows the electrical components to be seen while the enclosure's door is closed

The user can monitor the status of the components without the need for opening the enclosure's door maintaining the ingress protection

Materiale: Stainless Steel 304

Finish: Poleret

Tykkelse: 1.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Antal låse	Window Size	Produktfamilie	Enclosure Material
ADCS03624	360mm	240mm	1	219 x 83mm	Wall Mounted	Lakeret Stål
ADCS04030	400mm	300mm	1	259 x 143mm	Wall Mounted	Lakeret Stål

Katalognummer	Højde	Bredde	Antal låse	Window Size	Produktfamilie	Enclosure Material
ADCS04040	400mm	400mm	1	259 x 243mm	Wall Mounted	Lakeret Stål
ADCS04060	400mm	600mm	1	259 x 443mm	Wall Mounted	Lakeret Stål
ADCS05040	500mm	400mm	1	359 x 243mm	Wall Mounted	Lakeret Stål
ADCS05050	500mm	500mm	1	359 x 343mm	Wall Mounted	Lakeret Stål
ADCS06040	600mm	400mm	2	459 x 243mm	Wall Mounted	Lakeret Stål
ADCS06060	600mm	600mm	2	459 x 443mm	Wall Mounted	Lakeret Stål
ADCS06080	600mm	800mm	2	459 x 643mm	Wall Mounted	Lakeret Stål
ADCS08060	800mm	600mm	2	659 x 443mm	Wall Mounted	Lakeret Stål
ADCS08080	800mm	800mm	2	659 x 643mm	Wall Mounted	Lakeret Stål
ADCS10080	1000mm	800mm	1	859 x 643mm	Wall Mounted	Lakeret Stål
ADCS12080	1200mm	800mm	1	1059 x 643mm	Wall Mounted	Lakeret Stål
ADCS14080	1400mm	800mm	1	1259 x 643mm	Wall Mounted	Lakeret Stål

YDERLIGERE PRODUKTOPLYSNINGER

* 3-punkts espagnoletlås. Ikke velegnet til AFS.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.