


Bæreskinne til tungt udstyr, CBU



Denne kraftige bærestang til montering af tunge komponenter som f.eks. transformatorer, leveres med T-formede glidebolte og er forsynet med langhuller for montering i enhver position i skabet.

FUNKTIONER

Beskrivelse: Bæreskinne til tungt udstyr til montering af tunge komponenter som f.eks. transformere. Udstyret med T-formede glidebolte og slidser til montering i alle positioner, både i skabets bredde og dybde.

Materiale: 2.5 mm forzinket stål.

Pakke størrelse: 1 sæt med monteringsmateriale og 4 T-formede glidebolte.

Materiale: Lakeret Stål
Finish: Forzinket Stål
Tykkelse: 2.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Load Rating	Enclosure Material
CBU1000	49mm	1000mm	31mm	1800N	Lakeret Stål
CBU1200	49mm	1200mm	31mm	1500N	Lakeret Stål
CBU400	49mm	400mm	31mm	3000N	Lakeret Stål
CBU500	49mm	500mm	31mm	3000N	Lakeret Stål
CBU600	49mm	600mm	31mm	3000N	Lakeret Stål
CBU800	49mm	800mm	31mm	2250N	Lakeret Stål

YDERLIGERE PRODUKTOPLYSNINGER

Maximum last pr. bar.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.